



PHARMACEUTICAL HOSES IN SILICONE, EPDM AND PFA

For applications in the pharmaceutical and biotech industries.



CONNECT THE WAY YOU WANT.

The flexible Dockweiler connection that connects seamlessly.

As a manufacturer of high purity stainless steel tube systems, Dockweiler has been familiar with the requirements of the pharmaceutical industry for decades. Having added a new range of elastomeric and thermoplastic hoses, we are now able to offer our customers complete hose systems as a one-stop provider.

As always, these products meet the well known Dockweiler quality standards.

The advantages at a glance:

- Dockweiler supplies all hose systems as a one-stop provider, ensuring that your particular system is optimally configured.
- All hoses and fittings are made of high-quality materials.
- Full traceability across all stages of manufacture.
- High quality crimping that minimizes gaps.
- The hoses are freely configurable, i.e. the fittings can be combined with the hoses as desired.
- Fast processing and delivery.
- Optional: PolyFlow PTR hoses crimped without dead space no gap up to the seal.





Available hose types:

- **PolyFlow ST** *Platinum-cured silicone,* braid-reinforced
- **PolyFlow STR** Platinum-cured silicone, braid-reinforced with stainless steel wire reinforcement
- **Polyflow ETR** –Braid-reinforced and with stainless steel wire reinforcement, outside blue EPDM, inside food grade white EPDM
- 4 PolyFlow PTR OHM Black, electrically conductive PTFE (Teflon®) inside, EPDM, fabric and >1» also stainless steel wire reinforced outside
- **PolyFlow PTR** Inside white PTFE (Teflon®), outside EPDM, reinforced with fabric and >1 also with stainless steel wire



Available connections:

D

- **TriClamp connections** in accordance with DIN 32676 and ASME BPE 2016 Materials: 1.4404 / UNS S31603 (316L), optionally 1.4435 / UNS S31603 (316L)
- **Aseptic connections** in accordance with DIN 11864 Form A, all versions. Material: 1.4435 / UNS S31603 (316L)
- **Welding ends** for orbital welding. Material: 1.4435 / UNS S31603 (316L)
- **ZeroCon connection with no dead space** *Material*: 1.4435 / UNS S31603 (316L)
- **Further connections** on request

Inner surface roughness \leq 0.8 μ m, also lower on request and with electropolished surface

2

QUALITY PLUS FLEXIBILITY.

The advantages of Dockweiler hoses at a glance.



Construction

Outside and inside consisting of high purity silicone. High-heat resistant braid insert.

Applications

Suitable for pharmaceutical, biotech, cosmetic, and food applications, even at high temperatures (injection products, blood plasma, high purity water, and liquid food-stuffs). Not suitable for vacuum applications.

	Available Sizes		
	¹ / ₄ " - 1", bei Bedarf weitere Abmessungen		
	Maximum length	min. Bending radius	
	25 m, from a diameter of 25 mm 10 m only	40 mm (1/4") - 120 mm (1")	
	Temperature range	Working pressure	
	- 60° bis + 180°C	6.0 bar (1/4") - 2.5 bar (1")	

Available sine

Cleaning options

Sterilizable with steam (40 min, 3 bar at 124°C) or radiation, autoclavable

Conformity

FDA 21 CFR - 177 2600, BgVV Type II, USP class VI, USP Physicochemical 661, Cytotoxicity, Hemolysis, European Pharmacopoeia 3.1.9.



Construction

Exterior and interior made of high purity silicone, platinum cured. High-heat resistant textile insert, reinforced with stainless steel wire spiral.

Applications

Suitable for pharmaceutical, biotech, cosmetic, and food applications even at high temperatures (injection products, blood plasma, high purity water, and liquid food-stuffs).

Verfügbare Abmessungen			
¹ / ₂ "- 2", bei Bedarf weitere Abmessungen			
Maximum length	min. Bending radius		
40 m	60 mm (¹ / ₂ ") - 210 mm (2")		
Temperature range	Working pressure		
- 60° bis + 200°C	6.5 bar (1/4") - 6 bar (2")		

Cleaning options

Sterilizable with steam (40 min, 3 bar at 124°C) or radiation, autoclavable

Conformity

FDA 21 CFR - 177 2600, USP Klasse VI, 3-A Sanitary Standard, EC 1935/2004, EC 2023/2006, DM21/03/1973, BfR XV and XXI cat.2, ISO 10993-8, -10 and -11



Construction

Inside white food grade EPDM, outside blue EPDM plastic, fabric and stainless steel wire reinforced.

Application

All food applications, including in the high temperature range

Available sizes			
$^{3}/_{4}$ " - 2", other sizes as required			
)			

Cleaning options

Sterilizable with steam (40 min, 3 bar at 124°C) or radiation, autoclavable

Conformit

FDA 21CFR - 177 2600, BGVV Type II, USP Physicochemical 661



Construction

Inside smooth PFA, outside high purity, platinum-cured silicone. High-heat resistant braid insert, reinforced with stainless steel wire spiral.

Applications

Suitable for transporting food, chemical, cosmetic, pharmaceutical, and biotech products. Excellent thermal properties, even with very aggressive media. Avoids risk of degradation and product contamination. Very resistant to repeated dynamic processes. Frequently used in dosing and filling systems.

min. Bending radius
110 mm (¹ / ₂ ") - 210 mm (2")
Working pressure
6.5 bar (1/2" - 2")

Cleaning options

Sterilizable with steam (30 min, at 130°C), autoclavable

Conformity

FDA 21 CFR - 155 1550, USP Klasse VI, BFR XXI, EC 10/2011, 1282/2011, 1183/2011, 202/2014, 1935/2004, 2023/2006, Bed.Ggst V, 24.6.2013, LFGB



Construction

Inside smooth PFA, fully fluorinated, antistatic (R \leq 10 6 Ohm) outside smooth marble finished, patented, antistatic (R \leq 10 6 Ohm). High-heat resistant braid insert, reinforced with stainless steel wire spiral.

Applications

Suitable for transporting food, chemical, cosmetic, pharmaceutical, and biotech products. Excellent thermal properties, even with very aggressive media. Avoids risk of degradation and product contamination.

Dead space free flared version for applications with highest cleanliness requirements.

Maximum length min. Bending radius 40 m 110 mm (1/2") - 210 mm (2") Temperature range Working pressure - 30° to + 150°C 6.5 bar (1/2" - 2")

Available sizes

 $^{1}/_{2}" - 2"$

Cleaning options

Sterilizable with steam (30 min, at 130°C), autoclavable

Conformity

FDA 21 CFR - 155 1550, USP Klasse VI, BFR XXI, EC 10/2011, 1282/2011, 1183/2011, 202/2014, 1935/2004, 2023/2006, Bed.Ggst V, 24.6.2013, LFGB

4 5

NO GAP UP TO THE SEAL.


ELAFLEX technology for highest purity.

GAP-FREE DUE TO SPECIALLY PRESSED HOSE FITTING

For high-purity applications in the pharmaceutical industry and biotechnology, we offer PolyFlow-PTR "FLARED" and PolyFlow-PTR OHM "FLARED" tubing with ELAFLEX technology – a specially swaged tubing fitting with a flanged PTFE liner.

The homogeneous elastomer hose construction with smooth PTFE liner (Teflon®) is designed to meet the highest demands for cleanliness, hygiene and easy cleaning. The connection fitting has no contact with the medium, as the special compression allows no gap or dead space up to the seal. Each pressed stainless steel hose fitting has a corresponding marking.

The hoses can be cleaned quickly and easily. This saves time and costs.



CONNECTING FLOW TO PURITY – FOR MORE THAN 60 YEARS

Dockweiler has been a leading manufacturer of stainless steel tube systems for over 60 years. The company is known worldwide for the highest quality: in our tubing systems, in our advice and in our service.

With the same claim, Dockweiler now also offers plastic tubing for the pharmaceutical industry and biotechnology.







Cutting-edge technology from Elaflex:
The specially pressed hose fitting with flanged
PTFE liner «FLARED» is completely free of dead space.

Easy cleaning and fast residual emptying save time and costs.



Your local office

Dockweiler AG

An der Autobahn 10/20 19306 Neustadt-Glewe Germany

 Phone:
 + 49 38757 58-0

 Fax:
 + 49 38757 58-222

 E-mail:
 sales@dockweiler.com

 Web:
 www.dockweiler.com

