

TECHNICAL DATA SHEET

PMA Automation - BSH - Tube clamp

One-piece

PMA



CE FR

Applications:

• In automation applications for guiding or fixing PMA conduits

Features & Benefits:

- Single-piece, robust construction
- · Easy installation
- To be used in combination with standard halfshells BGN
- Space saving design allows optimum installation in automation applications
- Reduces mechanical stress on the cable harness extending the lifespan of the application
- Increased freedom of movement for cable looms with individual combination of functional inserts:
 - swivel base DKLK
 - ball joint half-shells BSSK
 - ball joint sleeve BTK
 - ball joint termination BKE
 - half-shells BGS for BKS cable star

Materials:

· High-grade, specially formulated polyamide 6

Compatible with:

- PMAFLEX Pro Conduits
- PMAFLEX Multilayer Conduits
- PMAFLEX Conduits

Weathering resistance:

• Very good UV resistance and weathering characteristics

Colour:

• Black

Chemical properties:


 Please refer to www.pma.ch (Technical Information / Chemical Resistance)


Environmental properties:


- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:												
Part no.	Fits to half-shells		Conduit size	Dimensions in mm (nom.)						Weight	Packing unit	
black	strain relief	slide	NW	ID	А	В	С	D	*E	Н	kg/100 pcs	pcs/PU
BSH-R23	BGN-S23T		23	34.9	63.3	26.0	30.0	_	34.0	60.5	3.6	30
BSH-R23.	BGN-S23G		23	34.9	63.3	26.0	30.0	-	34.0	60.5	3.6	30
BSH-R29	BGN-S29T		29	41.3	70.3	26.0	30.0	-	34.0	67	4.0	30
BSH-R29.	BGN-S29G	BGN-R29	29	41.3	70.3	26.0	30.0	-	34.0	67	4.0	30
BSH-R36	BGN-S36T		36	49.1	81.6	26.0	30.0	-	36.0	77.5	5.5	20
BSH-R36.	BGN-S36G	BGN-R36	36	49.1	81.6	26.0	30.0	-	36.0	77.5	5.5	20
BSH-R48	BGN-S48T		48	61.0	95.8	26.0	30.0	-	34.0	91	8.0	20
BSH-R48.	BGN-S48G	BGN-R48	48	61.0	95.8	26.0	30.0	-	34.0	91	8.0	20
BSH-R56	BGN-S56G	BGN-R56	56	75.5	112.6	30.0	60.0	30.0	38.0	109.8	11.5	20
BSH-R70	BGN-R70G	BGN-R70	70	96.5	148	39.5	60.0	30.0	45.0	142.5	24.0	20

* Width dimension over half-shell
Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time









Examples for combination possibilities:

The BSH tube clamp can be used to suit the application with different inserts.





Mechanical Properties:	Value: Test paramet	ters: Test method:
Tensile modulus	1'200 3'700 N/mm²	ISO 527
Tensile strength	45 65 N/mm²	ISO 527
Notched bar impact test	4 20 kJ/m²	ISO 180/1C
Vibration and shock standard	Cat. 2	IEC 61373, IEC 60068-2-27 / -64

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	−50 +105°C		PMA DO 9.21-4510
Upper application temperature	+120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+160°C	(168 h)	PMA DO 9.21-4360

Content of delivery:

- Tube clamp,
- PT-screw, stainless steel
- Straight pin

Assembly instructions:

• Possible combinations, please see on page 3

