

### Tooth sensor module with integrated magnet

The sensor modules of the GLM700ASB-Ax family are designed for use with passive measurement scales. The modules combine a GiantMagnetoResistive (GMR) tooth sensor with an integrated bias magnet in a compact SMD housing, to reduce the design and assembly effort of the user. In addition, the integration of sensor and magnet provides a very high quality of the sensor signals.

Adapted to a variety of tooth pitches, the integrated GMR sensors apply the FixPitch technology. This means that the sensor chip is matched to a given tooth pitch.

In use with a ferromagnetic scale and a matching pitch, the module delivers two 90 degree phase shifted analogue signals (sine and cosine).

The table "Product overview" on page 7 shows the modules available with the according pitch.



Article description	Package
GLM7xxASB-Ax 1)	Module Combining a sensor and a magnet for a variety of tooth pitches with sine and cosine output signal.

 $<sup>^{\</sup>mbox{\tiny 1)}}$  For order information see page 7.

#### **Quick Reference Guide**

Symbol	Parameter	Min.	Тур.	Max.	Unit
V <sub>CC</sub>	Supply voltage	-	5.0	-	V
V <sub>peak</sub>	Signal amplitude per V <sub>CC</sub> 2)	4.0	9.0	20.0	mV/V
T <sub>amb</sub>	Ambient temperature	-40	-	+125	°C
f	Frequency range	1	-	-	MHz


<sup>&</sup>lt;sup>2)</sup> The amplitude depends on the distance between sensor and scale. For further information see fig. 6 (page 4).

### **Absolute Maximum Ratings**

In accordance with the absolute maximum rating system (IEC60134).

Symbol	Parameter	Min.	Max.	Unit
V <sub>CC</sub>	Supply voltage	-9.0	+9.0	V
T <sub>amb</sub>	Ambient temperature	-40	+125	°C
T <sub>stg</sub>	Storage temperature	-40	+125	°C
MSL	Moisture sensitivity level	2		

Stresses beyond those listed under "Absolute maximum ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.



#### **Features**

- Gear tooth sensor with integrated magnet
- Differential sine and cosine output signals
- Ambient temperature range from -40 °C to +125 °C
- Designed for vertical or horizontal mounting
- High signal quality due to FixPitch technology
- Contactless, wear-free measurement

### **Advantages**

- Allows use of simple passive toothed structures as measurement scale; so reducing design, manufacturing and assembly effort
- Flexible design options due to identical pin arrangements
- Reliable operation in difficult environments
- High interpolation possible within tooth pitch for high resolution and high accuracy
- Minimal offset voltage
- Low power consumption for battery-driven applications

### **Applications**

Incremental encoder for linear or rotary motion in various industrial applications, for example:

- Linear position measurement
- Linear and rotary bearings









Tooth sensor module with integrated magnet

### **Electrical Data**

T<sub>amb</sub> = 25 °C; unless otherwise specified.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
V <sub>CC</sub>	Supply voltage		-	5.0	-	V
TC <sub>RB</sub>	Temperature coefficient of R <sub>B</sub> and R <sub>S</sub> <sup>1)</sup>	T <sub>amb</sub> = (-40+125) °C	-	0.12	-	%/K
TC <sub>Voff</sub>	Temperature coefficient of V <sub>off</sub> <sup>2)</sup>	T <sub>amb</sub> = (-40+125) °C	-3.0	-	+3.0	μV/V/K
T <sub>amb</sub>	Ambient temperature		-40	-	+125	°C
V <sub>peak</sub>	Signal amplitude per V <sub>CC</sub> 3)		4.0	9.0	20.0	mV/V
TC <sub>Vpeak</sub>	Temperature coefficient of V <sub>peak</sub> <sup>4)</sup>	T <sub>amb</sub> = (-40+125) °C	-0.08	-0.12	-0.16	%/K
f	Frequency range 5)		1	-	-	MHz

$$^{1)} \quad TC_{R} = 100 \cdot \frac{R_{(T2)} - R_{(T1)}}{R_{(Tref)} \cdot (T_{2} - T_{1})} \quad \text{with} \quad T_{1} = -40^{\circ}C, T_{2} = +125^{\circ}C \quad \text{and} \quad T_{ref} = +25^{\circ}C$$

$$^{4)} \quad TC_{Vpeak} = 100 \cdot \frac{V_{peak(T2)} - V_{peak(T1)}}{V_{peak(Tamb)} \cdot (T_2 - T_1)} \quad \text{with} \quad T_1 = +25^{\circ}C, T_2 = +125^{\circ}C$$

### **Product Type Specific Data**

Article description	Pitch	Offset Voltage	Bridge resistance 6)	Sensor resistance 7)	Air gap <sup>8)</sup>
GLM711ASB-Ax	1 mm	± 3.0 mV/V	5.5 kΩ	2.75 kΩ	200 µm
GLM712ASB-Ax	2 mm	± 3.5 mV/V	5.7 kΩ	2.85 kΩ	400 μm
GLM713ASB-Ax	3 mm	± 3.5 mV/V	5.7 kΩ	2.85 kΩ	600 µm
GLM714ASB-Ax	0.94 mm (module 0.3)	± 3.0 mV/V	5.6 kΩ	2.80 kΩ	190 µm
GLM715ASB-Ax	1.57 mm (module 0.5)	± 3.0 mV/V	5.8 kΩ	2.90 kΩ	310 µm

 $<sup>^{\</sup>mbox{\tiny 6)}}$  Bridge resistance between pad 1 and 5, 2 and 6. Resistor tolerance  $\pm 15~\%.$ 

 $<sup>^{2)}\</sup>quad TC_{Voff}=100\cdot \frac{V_{off(T2)}-V_{off(T1)}}{T_{2}-T_{1}}\quad \text{with}\quad T_{1}=-40^{\circ}C, T_{2}=+125^{\circ}C$ 

<sup>&</sup>lt;sup>3)</sup> The amplitude depends on the distance between sensor and scale. See Fig. 1 (page 4) for more information.

<sup>5)</sup> No significant amplitude loss in this frequency range.


 $<sup>^{7)}</sup>$  Sensor resistance between pad 3 and 4. Resistor tolerance  $\pm 15$  %.


 $<sup>^{\</sup>mbox{\tiny 8)}}$  Optimal air gap between sensor and scale - for further information see Fig. 6 (page 4).




Tooth sensor module with integrated magnet

### **Additional Sensor Information**




















Fig. 5: Passive measurement scales. In addition to gear teeth a variety of other tooth-like structures can be used with the GLM tooth sensor module.

### Module vs. Tooth Pitch

To calculate the modules or the tooth pitch you can use these formula:

$$m = \frac{d}{z} = \frac{p}{\pi}$$

m = module of the gearwheel


d = reference diameter (in mm)

z = number of teeth on the perimeter

p = tooth pitch (in mm)

Tooth sensor module with integrated magnet

### **Typical Performance Graphs**








Fig. 7: Typical sensor output signal at a rectangular shaped tooth structure as a function of the tooth height.








Tooth sensor module with integrated magnet

### **Pinning**

	<b>'</b>	
Pad	Symbol	Parameter
1	+V <sub>O1</sub>	Positive output voltage bridge 1
2	+V <sub>O2</sub>	Positive output voltage bridge 2
3	V <sub>CC</sub>	Supply voltage
4	GND	Ground
5	-V <sub>O1</sub>	Negative output voltage bridge 1
6	-V <sub>O2</sub>	Negative output voltage bridge 2



### **Dimensions**




Fig. 11:

PCB outline (all dimensions in mm unless otherwise specified).



Tooth sensor module with integrated magnet

Recommended tooth profiles	h tooth height	w tooth top land width	g tooth gap	d air gap	signal quality
Pach = p  GLM Modul  d  h	≥ <del>p</del> 4	~ <del>p</del> 3	~ <sup>2p</sup> / <sub>3</sub>	~ <mark>p</mark> 5	+++
Pitch = p GLM Modul	≥ <del>p</del> /4	~ <sup>p</sup> / <sub>3</sub>	~ <sup>2p</sup> / <sub>3</sub>	~ <mark>P</mark> 5	+++
Pitch = p  GLM module  d L  w g	≥ <del>p</del> /4	~ <del>p</del> 3	~ <sup>2p</sup> 3	~ <mark>P</mark> 5	+++
Pitch p  GLM module	≥ <del>p</del> 3	-	-	~ <mark>p</mark> 5	++

Magnetically soft materials are to be used for the measurement scale, e. g.:

Material short designation	Material number according DIN 17007 T1
St37	(1.0037)
St44	(1.0044)
9SMnPb28	(1.0718)
9SMnPb29	(1.0737)
20MnV6	(1.5217)

The tooth gap can be filled by a chrome coating or by other non-ferromagnetic materials if the application requires a smooth surface. This table is intended only as a rough guide. Please contact your sales engineer for further details.

Material short designation	Material number according DIN 17007 T1
X20Cr13	(1.4021)
X30Cr13	(1.4028)
X46Cr13	(1.4034)
X6Cr17	(1.4016)
X14CrMoS17	(1.4104)
X17CrNi16 2	(1.4057)
X39CrMo17 1	(1.4122)
X90CrMoV18	(1.4112)




Tooth sensor module with integrated magnet

### **Purchased Parts Package and Delivery Form**

Quantity	Part	Description
20	GLM7xxASB-AC	Waffle pack for horizontal mounting
120	GLM7xxASB-AH	Tray for vertical mounting

### **Order Code**



### **Product Overview**

Article description	Pitch	Marking 1)	Delivery form 2)	Article number
GLM711ASB-AC	1 mm	B\$&	Waffle Pack	5102.2211.2
GLM712ASB-AC	2 mm	E\$&	Waffle Pack	5102.2212.2
GLM713ASB-AC	3 mm	F\$&	Waffle Pack	5102.2213.2
GLM714ASB-AC	0.94 mm (module 0.3)	A\$&	Waffle Pack	5102.2214.2
GLM715ASB-AC	1.57 mm (module 0.5)	D\$&	Waffle Pack	5102.2215.2
GLM715ASB-AH	1.57 mm (module 0.5)	D\$&	Tray	5102.2225.1

<sup>&</sup>lt;sup>1)</sup> \$ - calender week (A:1/2, B:3/4, ...), & - Year (E:2013, F:2014, ...).

Note: For all GLM700 types delivery form "Tray" (for vertical mounting) is available on request.

The delivery form "Tray" is used for the automatic vertical assembly of the GLM module.



Tooth sensor module with integrated magnet

### **Special Design Features**



Sensors with PerfectWave design provide the best signal quality, highest accuracy and optimal sensor linearity by filtering out higher harmonics in the signal. The linearity of the sensor is assured, even for weak magnetic field measurement.



FixPitch sensors are adapted to the pole length (pitch) of the measurement scale. The linearity of the sensor is optimized and the influence of interference fields is minimized.



Tooth sensor module with integrated magnet

### **General Information**

#### **Product Status**

Article	Status
GLM7xxASB-Ax	The product is in series production.
Note	The status of the product may have changed since this data sheet was published. The latest information is available on the internet at www.sensitec.com.

#### **Disclaimer**

Sensitec GmbH reserves the right to make changes, without notice, in the products, including software, described or contained herein in order to improve design and/or performance. Information in this document is believed to be accurate and reliable. However, Sensitec GmbH does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Sensitec GmbH takes no responsibility for the content in this document if provided by an information source outside of Sensitec products.

In no event shall Sensitec GmbH be liable for any indirect, incidental, punitive, special or consequential damages (including but not limited to lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) irrespective the legal base the claims are based on, including but not limited to tort (including negligence), warranty, breach of contract, equity or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Sensitec product aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the General Terms and Conditions of Sale of Sensitec GmbH. Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Unless otherwise agreed upon in an individual agreement Sensitec products sold are subject to the General Terms and Conditions of Sales as published at www.sensitec.com.



Tooth sensor module with integrated magnet

#### **General Information**

### **Application Information**

Applications that are described herein for any of these products are for illustrative purposes only. Sensitec GmbH makes no representation or warranty – whether expressed or implied – that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Sensitec products, and Sensitec GmbH accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Sensitec product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Sensitec GmbH does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Sensitec products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s).

Sensitec does not accept any liability in this respect.

#### **Life Critical Applications**

These products are not qualified for use in life support appliances, aeronautical applications or devices or systems where malfunction of these products can reasonably be expected to result in personal injury.

### Copyright © 2019 by Sensitec GmbH, Germany

All rights reserved. No part of this document may be copied or reproduced in any form or by any means without the prior written agreement of the copyright owner. The information in this document is subject to change without notice. Please observe that typical values cannot be guaranteed. Sensitec GmbH does not assume any liability for any consequence of its use.